



SideKick Controller.  
Power supply not shown.

# SIDEKICK™ QCL CONTROLLER

## MULTI-FUNCTION, QCL CONTROLLER WITH INDUSTRY LEADING NOISE PERFORMANCE

SideKick is a next-generation design that builds on the field-proven success of our TLC/FLC control electronics. SideKick supports Daylight's broad range of external cavity quantum cascade laser (ECqCL™) systems<sup>[2]</sup>, functionality, and QCL wavelength selection. SideKick represents a significant evolution in controller features and performance, and is compatible with all Daylight's 31/41xxx tunable and fixed-wavelength laser heads<sup>[2]</sup>. SideKick allows flexible, high-precision and high-stability control of laser: output power; wavelength; temperature; scan speed (to  $>5000 \text{ cm}^{-1}/\text{s}$ <sup>[3]</sup>); pulse width, repetition rate and duty cycle (up to 1  $\mu\text{s}$ , 3 MHz and 30% respectively)<sup>[3,4]</sup>. And all while protecting your gain chip with Daylight's proven High-Fidelity Quantum Cascade Drive (HFQD™) circuitry.

Signal-to-Noise is critical in most MWIR applications, and laser performance is only as good as controller performance. Recognizing this, SideKick's design emphasizes low noise and, when paired with a suitable laser head, produces extremely low RIN<sup>[5]</sup>. With a compact form factor and USB/Ethernet connectivity, SideKick is ideally suited to OEM integration and laboratory use. The included GUI<sup>[6]</sup> and SDK provide

elegant local/remote control, error messaging, and also allow user-programmable tuning, swept scans, step-and-measure scans, and multiple triggering modes. With a SideKick in your Daylight laser system, you'll find your mid-infrared applications easier than ever before. Just connect SideKick to your PC, laser head and go!

### HIGHLIGHTS

- OEM or laboratory use
- Supports CW or pulsed laser operation
- Integrated laser power, tuning, and temperature control
- Ultra-low current noise enables ultra-low optical RIN
- USB/Ethernet connectivity with GUI and SDK included for robust local/remote control
- Field-tested HFQD circuitry for chip protection
- Remote diagnostics and error messaging for rapid troubleshooting

# COMPACT, LOW NOISE CONTROLLER

## SIDEKICK SPECIFICATIONS

### PERFORMANCE SPECIFICATIONS<sup>[1]</sup>

Modes of Operation	Pulsed, CW, CW-Mode-Hop-Free
Compatibility	31xxx/41xxx tunable & fixed- $\lambda$ laser heads <sup>[2]</sup>
Tuning Modes	Set wavelength, uni- and bi-directional scans, step and measure, start/stop scan <sup>[3]</sup>
External Interfaces	USB 2.0, Ethernet 10/100
Control Interfaces	GUI and SDK command set (included)

### ELECTRICAL PARAMETERS

Current Accuracy	0.75% of requested current
Current Precision	1 mA
Pulse Width <sup>3</sup>	Supports 40 ns to 1 $\mu$ s <sup>[3,4]</sup> , 20-ns steps
Pulse Repetition Rate <sup>3,4</sup>	Supports 0.1 kHz to 3 MHz
Maximum Duty Cycle	10% (option: up to 30% – please inquire) <sup>[3,4]</sup>
Temperature Adjust	$\pm 5$ °C programmable
Scan Speed <sup>3</sup>	Supports > 5000 $\text{cm}^{-1}/\text{s}$ (max.), 0.5 $\text{cm}^{-1}/\text{s}$ (min.) <sup>[3]</sup>
Triggered	Internal clock, external trigger (External Pulse, External Trigger)
Trigger Input	TTL
Current Modulation	Not included (applied direct to laser head) <sup>[3]</sup>
Input Power A, 22–30 VDC)	90–264 VAC, 47–63 Hz with included AC-DC Power Supply (or <3
Cooling	Passive air, no fans <sup>[4]</sup>
Regulatory Compliance	CDRH, CE <sup>[3]</sup>
Temperature Range	10–40°C (operation); -20–60°C (stored)
Humidity	0–80% RH, non-condensing
Size	Sidekick: 7.3 x 5.2 x 1.4 ins (18.5 x 13.2 x 3.5 cm) Power Supply: 2.7 x 5.2 x 1.6 ins (6.9 x 13.2 x 4.1 cm)

<sup>[1]</sup> All specifications are: defined after a 10-minute warm up; subject to change without notice.

<sup>[2]</sup> Not compatible with 11/21xxx laser heads, which require designated TLC/FLC controllers.

<sup>[3]</sup> Requires suitable laser head and/or gain chip - please inquire.

<sup>[4]</sup> Laser operation above 10% duty cycle and/or 3 MHz repetition rate requires a suitable QCL chip and may require supplemental cooling of the laser head - please inquire.

<sup>[5]</sup> Typical RIN as low as -150 dBc/Hz was measured in the range of 400 kHz to 1 MHz using SideKick with a TLH-41060-MHF laser head.

<sup>[6]</sup> GUI compatible with Windows® 7, 8.1 & 10. Please inquire for other OS.

COMPLIES WITH 21 CFR 1040.10 AND 1040.11 EXCEPT FOR DEVIATIONS PURSUANT TO LASER  
NOTICE NO. 50, DATED JUNE 24, 2007. COMPLIES WITH IEC 60825-01

The information in this data sheet is to the best of our knowledge, accurate as of the date of issue. Leonardo DRS reserves the right to change this information without notice. Nothing herein shall be deemed to create any warranty, expressed or implied. Copyright © Leonardo DRS 2018 All Rights Reserved.



REV 2-2018